

CommScope® Cabinets and Accessories

North, Central and South America Regions



NETWORK CABINET



SERVER CABINET

	NETWORK CABINET	SERVER CABINET
Key Features	Strong yet lightweight frame construction	Strong yet lightweight frame construction
	Supplied fully assembled	Supplied fully assembled
	Load-rated up to 3200 lb	Load-rated up to 3200 lb
	Fully adjustable front and rear vertical mounting rails	Fully adjustable front and rear vertical mounting rails
Applications	Network Switches Data Centers	Server Rooms and Closets Data Centers
Rack Unit Height	42U	42U, 47U
Overall Cabinet Height	2000 mm / 78.8 in	2000 mm / 78.8 in 2200 mm / 86.6 in
Width	800 mm / 32 in 600 mm / 24 in	600 mm / 24 in 800 mm / 32 in
Depth	800 mm / 32 in	1000 mm / 40 in 1200 mm / 48 in
Load Rating	3200 lb / 1451 kg	3200 lb / 1451 kg
Front Door	Viewing Perforated Door or Fully Perforated Door	Fully Perforated Door
Rear Door	Split Perforated Door	Split Perforated Door
Sides	Order Solid Side Panels Separately	Order Solid Side Panels Separately
Top	Included	Included
Material Type	Welded Steel Frame	Welded Steel Frame
Accessories	Range of accessories available for various installation needs	Range of accessories available for various installation needs