

Sureflex™ Assembly Part Number Description

F4 -		A -	NM -	DM -	3 -	M -	5 -	P
Abbreviation	Cable	Cable Assembly Process Options	Connector 1	Connector 2	Assembly Length Options:	Unit of Measure for Cable Length	Decimal Length Options	Cable Assembly Performance Grade Options
F4	FSJ4-50	A = Sureflex	DM = 7-16 DIN Male		Length in Feet or Meters	Null = Feet	Length in 10ths	Null = Standard
L4	LDF4-50	Null = Standard	DF = 7-16 DIN Female			M = Meters	Null = 0	P = Premium
F1	FSJ1-50		DR = 7-16 DIN Right Angle				1 = .1 ft or M	
F2	FSJ2-50		NM = Type N Male				2 = .2 ft or M	
L1	LDF1-50		NF= Type N Female				3 = .3 ft or M	
L2	LDF2-50		NR= Type N Right Angle				4 = .4 ft or M	
F4RN	FSJ4RK-50		SM = SMA Male				5 = .5 ft or M	
L4RN	LDF4RK-50		TM = TNC Male				6 = .6 ft or M	
F1RN	FSJ1RK-50		BDF 7-16 DIN Bulkhead female				7 = .7 ft or M	
F2RN	FSJ2RK-50		BNF Type IN Bulkhead female				8 = .8 ft or M	
L1RN	LDF1RK-50						9 = .9 ft or M	
L2RN	LDF2RK-50							