

## SureFlex™ Premium Cable Assemblies and Rapid Response Program (North America)

To meet today's needs for top electrical performance and rapid delivery in wireless base station products, Andrew Solutions has streamlined the top performing SureFlex cable assembly product line.

**SureFlex Premium Cable Assemblies will provide the following performance advantages:**

- Guaranteed PIM of -116dBm/-159dBc
- Guaranteed VSWR of 1.06
- Guaranteed DTF of -34 dB
- Online factory test data for each assembly

(<http://www.commscope.com/assemblydata>)



Based on the SureFlex -3GSH Series cable assemblies, the new -P Premium Series utilizes the same robust factory automated soldered process and 100% testing and data storing processes.

### Rapid Response Program

To meet unpredictable construction schedules, the most vital cable assembly configurations are stocked at Andrew Solutions' distribution centers in the U.S. and are available for immediate delivery. This program is available for the cable assemblies listed below for orders placed directly with Andrew.

- Same day shipment on orders placed by 10:00 a.m. local time
- Next day shipment on orders placed by 5:00 p.m. local time
- Shipment method per customer request (surface, air, pick-up)
- Andrew Distribution Centers are located in:
  - Joliet, Illinois
  - Euless, Texas
  - Sparks, Nevada

Visit our Web site at [www.commscope.com/andrew](http://www.commscope.com/andrew) or contact your local Andrew Solutions representative for more information.

© 2010 CommScope, Inc. All rights reserved. Andrew Solutions is a trademark of CommScope. All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to Andrew Solutions products or services.

(10/10) (CO-104446-EN)

## Essential Cable Assemblies Stocked for Rapid Response

### Part number

### Description

#### LDF4-50A, 1/2 Inch Cable Assemblies

L4A-DMDM-3-P	LDF4 Premium SureFlex assembly, 3 ft.
L4A-DMDM-6-P	LDF4 Premium SureFlex assembly, 6 ft.
L4A-DMDM-8-P	LDF4 Premium SureFlex assembly, 8 ft.
L4A-DMDM-10-P	LDF4 Premium SureFlex assembly, 10 ft.
L4A-DMDM-20-P	LDF4 Premium SureFlex assembly, 20 ft.
L4A-DM-30-P	LDF4 SureFlex assembly, 2nd conn ordered separately, 30 ft.

#### FSJ4-50A, 1/2 Inch Super flexible Cable Assemblies

F4A-DMDM-6-P	FSJ4 Premium SureFlex assembly, 6 ft.
F4A-DMDM-8-P	FSJ4 Premium SureFlex assembly, 8 ft.
F4A-DMDR-10-P	FSJ4 Premium SureFlex assembly, 10 ft.
F4A-DMDR-15-P	FSJ4 Premium SureFlex assembly, 15 ft.
F4A-DM-30-P	FSJ4 SureFlex assembly, 2nd conn ordered separately, 30 ft.

#### LDF4-50A, Field Fit Connectors and Tools

L4TDM-PSA	7-16 DIN male connector, LDF4
L4DR-PS	7-16 DIN male right angle connector, LDF4
L4TNM-PSA	Type N male connector, LDF4
L4NR-PS	Type N right angle male connector, LDF4
CPT-L4ARC1	Auto cable preparation tool, LDF4

#### FSJ4-50A, Field Fit Connectors and Tools

F4PDMV2-C	7-16 DIN male connector, FSJ4
F4DR-C	7-16 DIN male right angle connector, FSJ4
F4PNMV2-HC	Type N male connector, FSJ4
F4NR-HC	Type N right angle male connector, FSJ4
CPT-F4B	Auto cable preparation tool, FSJ4

For more information, please contact Chris Stockman at [christopher.stockman@andrew.com](mailto:christopher.stockman@andrew.com) or +1-779-435-6370.

Visit our Web site at [www.commscope.com/andrew](http://www.commscope.com/andrew) or contact your local Andrew Solutions representative for more information.

© 2010 CommScope, Inc. All rights reserved. Andrew Solutions is a trademark of CommScope. All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to Andrew Solutions products or services.

(10/10) (CO-104446-EN)