

PIII[®] 750 JCASS 75 Ohm Coaxial Cable Trunk & Distribution

1100 CommScope Place
Hickory, NC 28603
(800) 982-1708
(828) 324-2200
Fax: (828) 324-3400
Int'l Fax: (828) 323-4989
www.commscope.com
CommScope Properties, LLC
All Rights Reserved




PRODUCT DESCRIPTION: (UNDERGROUND CONSTRUCTION)
SOLID ALUMINUM TUBE SWAGED ONTO DIELECTRIC
CORE, FULLY BONDED COPPER CLAD CENTER CONDUCTOR,
MIGRA-HEAL™ FLOODING COMPOUND, MEDIUM DENSITY
PE JACKET

CENTER CONDUCTOR:
COPPER CLAD ALUMINUM
NOMINAL DIAMETER: 0.167" (4.24 mm)

DIELECTRIC:
MICRO-CELLULAR FOAM PE
NOMINAL DIAMETER 0.680" (17.22 mm)

SHIELD:
SOLID ALUMINUM TUBE
NOMINAL OUTER CONDUCTOR THICKNESS: 0.035" (0.91 mm)

JACKET:
MEDIUM DENSITY PE (FLOODED WITH MIGRA-HEAL™
FOR UNDERGROUND CONSTRUCTION)
NOMINAL JACKET THICKNESS: 0.035" (0.90 mm)
NOMINAL DIAMETER OVER FLOODED JACKET: 0.830" (21.08 mm)



MECHANICAL CHARACTERISTICS:
MINIMUM BEND RADIUS: STANDARD = 8.0" (20.3 cm)
MINIMUM BEND RADIUS: BONDED = 6.0" (15.2 cm)
MAXIMUM PULLING TENSION = 675 lbs. (306 kg)

Shipping Weight (lbs./kft): 268 - (kg/km): 399

ELECTRICAL CHARACTERISTICS:

CAPACITANCE: 15.3 ± 1.0 pf/ft. (50 ± 3.0 nf/km)
IMPEDANCE: 75 ± 2 Ohms
VELOCITY OF PROPAGATION: 87% NOMINAL
NOMINAL DC LOOP RESISTANCE @ 68°F: 0.76 Ohms/1000 ft. (2.55 Ohms/km)
ATTENUATION @ 68°F (20°C):

@ Frequency MHz	dB/100 ft. (MAX.)	dB/100 meters (MAX.)
5 MHz	0.11	0.36
55 MHz	0.37	1.21
83 MHz	0.46	1.51
211 MHz	0.74	2.43
250 MHz	0.81	2.66
300 MHz	0.89	2.92
350 MHz	0.97	3.18
400 MHz	1.05	3.44
450 MHz	1.12	3.67
500 MHz	1.18	3.87
550 MHz	1.24	4.07
600 MHz	1.31	4.30
750 MHz	1.48	4.86
865 MHz	1.61	5.28
1000 MHz	1.74	5.71



*Drawing not to scale.
Specifications subject to change.
Revision: 06/07/07*